



## *Aspheric Lenses available in a wide range.*

*Among the organic resin lenses, the lenses of aspherical geometry have gradually encroached on the market at the expense of the lenses of spherical geometry.*

*This has happened thanks of their lower weight, reduced thickness and to their high optical quality, which permits the reduction of various aberrations, including field curvature, astigmatism by oblique beams and the longitudinal spherical aberration.*



*IODA makes at it's production site, aspheric glass moulds with which it creates finished and semi finished lenses.*

*With the cooperation of the University of Padova, IODA has created a new software called "Ray Tracking" which permits to calculate with great precision the vision ray and therefore calculate the ideal aspheric correction so as to reduce to a minimum the above mentioned aberrations in every part of the lens.*

*The hyperbolic curve of IODA's lenses allows to produce elegant and refined glasses, even with lenses of significant power increasing at the same time the comfort for the wearer.*

*The finished lenses are available in 60 and 65mm diameter, the spheric power ranges from +1,00 to +8.00, with cylinder till 2,00 dioptries (until Sph +6,00 Cyl+2,00).*

*As all IODA 's production, also aspherical semi-finished and finished lenses are produced in Padua, by specialized technicians who follow all the production steps, including 100% control (we check every lens one by one).*



Hard resin aspheric lenses  $\varnothing$ 65 and 60mm

*Aspheric Lenses available in a wide range.*

Sph	Cyl								
	0,00	0,25	0,50	0,75	1,00	1,25	1,50	1,75	2,00
0,00									
+0,25									60
+0,50								60	60
+0,75							60	60	60
+1,00	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+1,25	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+1,50	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+1,75	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+2,00	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+2,25	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+2,50	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+2,75	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+3,00	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+3,25	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+3,50	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+3,75	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+4,00	65-60	65-60	65-60	65-60	65-60	60	60	60	60
+4,25	65-60	65-60	65-60	65-60	60	60	60	60	60
+4,50	65-60	65-60	65-60	60	60	60	60	60	60
+4,75	65-60	65-60	60	60	60	60	60	60	60
+5,00	65-60	60	60	60	60	60	60	60	60
+5,25	65-60	60	60	60	60	60	60	60	60
+5,50	65-60	60	60	60	60	60	60	60	60
+5,75	65-60	60	60	60	60	60	60	60	60
+6,00	65-60	60	60	60	60	60	60	60	60
+6,25	60	60	60	60	60	60	60	60	
+6,50	60	60	60	60	60	60	60		
+6,75	60	60	60	60	60	60			
+7,00	60	60	60	60	60				
+7,25	60	60	60	60					
+7,50	60	60	60						
+7,75	60	60							
+8,00	60								

*In each lens you can find all the commitment and knowledge of a company that puts the quality of its products as its principal objective.*

*for any other information you can contact me directly by mail at :*

[francesco.battisti@ioda-it.com](mailto:francesco.battisti@ioda-it.com)

*Sales and Customer Service Manager  
Francesco Battisti*